



## Type 2774/2776 DryLoc pH Electrodes

### pH/ORP:

- Wetted Materials: Ryton, PTFE, FKM, glass
- Connection: Durable DryLoc® with gold plated connections
- Compatible Preamp/Sensor Electronics: 2750 and 2760
- Compatible Instruments: Use the 2760 preamplifier with the Signet 8750; Use the 2750 sensor electronics with the Signet 8900, 9900 or 9950 instruments
- Additional Features: Quick temperature response and can be mounted upside-down
- In-line Mounting styles: Standard 3/4 inch or ISO threaded fittings
- Submersible mounting: Available using the back of the preamplifier or sensor electronics
- Applications: Water treatment, water quality monitoring, some harsh chemicals

MFR #	Style	Compatible Preamplifier	Mounting	Code
3-2774	Flat	2760 DryLoc	with threaded connection	<b>159 000 955</b>
3-2774-1	Flat	2751 DryLoc	with threaded connection	<b>159 000 956</b>
3-2776	Bulb	2760 DryLoc	with threaded connection	<b>159 000 959</b>
3-2776-1	Bulb	2751 DryLoc	with threaded connection	<b>159 000 960</b>
3-2774-HT	Flat	2751 DryLoc	with threaded connection	<b>159 001 796</b>
3-2774-HT-C	Flat	2751 DryLoc	with threaded connection	<b>159 001 795</b>
3-2774-HT-ISO	Flat	2751 DryLoc	with threaded connection	<b>159 001 794</b>

The technical data are not binding. They neither constitute expressly warranted characteristics nor guaranteed properties nor a guaranteed durability. They are subject to modification. Our General Terms of Sale apply.

Georg Fischer Piping Systems Ltd, Postfach, CH-8201 Schaffhausen/Switzerland Phone +41 -(0)52-631 1111 e-mail: [info.ps@georgfischer.com](mailto:info.ps@georgfischer.com) Internet: <http://www.gfps.com>